760 - 830 nm

830 - 920 nm

920 - 1100 nm

1100 - 1300 nm

1300 - 1450 nm

1450 - 1650 nm

1650 - 1850 nm

1850 - 1900 nm

1900 - 2200 nm

2200 - 2600 nm

2600 - 3000 nm

3000 - 6000 nm

DFB laser diodes from 2200 nm to 2600 nm

nanoplus single mode laser diodes

nanoplus is the only manufacturer worldwide routinely providing single and multi mode lasers at any wavelength from 760 to 6000 nm. At wavelengths up to 14 μ m, QCLs complete nanoplus' laser portfolio. Our patented distributed feedback laser diodes deliver single mode emission with well defined optical properties enabling a wide range of applications.

nanoplus lasers operate reliably in tens of thousands of installations worldwide, including chemical and metallurgical industries, gas pipelines, power plants, medical systems, airborne and satellite applications.

key features

- √ very high spectral purity
- √ narrow linewidth
- √ excellent reliability
- √ wide variety of packaging options
- √ customer-specific designs available



application areas

- high performance gas sensing for process and environmental control
- ✓ precision metrology
- √ atomic clocks
- √ spectroscopy
- √ space technology

nanoplus lasers with excellent performance are specifically designed and characterized to fit your needs. This data sheet summarizes typical properties of nanoplus DFB lasers in the range from 2200 nm to 2600 nm. In this wavelength regime e. g. CO, N_2O , C_2H_4 and CH_4 can be detected with particularly high sensitivity, since the detection sensitivity typically increases at long wavelengths. Overleaf data for DFB lasers used for CO detection is shown as an example.

general ratings (T = 25 °C)	symbol	unit	typical
optical output power	P _{out}	mW	3
reverse voltage	V_{r}	V	1.8
forward current	l _f	mA	100
side mode suppression ratio (SMSR)		dB	> 32

On request, lasers with specifically optimized properties, e. g. higher output power, are available.

laser packaging options
TO5.6 header with or without cap
TO5 header with TEC and NTC
butterfly housing with SM or PM fiber up to 2.33 μm

For dimensions and accessories, please see

Further packaging options available on request.

nanoplus DFB laser diodes at 2334 nm


A wide variety of gas molecules exhibit characteristic absorption lines in the near infrared. DFB lasers emitting at 2334 nm are perfectly suited for highly sensitive detection of CO concentrations. For this application, highly stable laterally and longitudinally single mode lasers are required.

This data sheet reports performance data of nanoplus DFB lasers at this wavelength. Similar performance data are obtained in the entire wavelength range from 2200 nm to 2600 nm. For examples of performance data of nanoplus lasers in other wavelength ranges,

Fig. 1 Room temperature cw spectrum of a nanoplus DFB laser diode operating at 2334 nm

In many applications, temperature and / or current variations are used to adjust the laser emission precisely to the target wavelength.

Fig. 2 Mode hop free tuning of a nanoplus 2334 nm DFB laser diode by current variation at different temperatures



electrooptical characteristics (T = 25 °C)	symbol	unit	min	typ	max
peak wavelength	λ	nm	2333	2334	2335
threshold current	I _{th}	mA	25	30	50
slope efficiency	е	mW/mA	0.10	0.15	0.20
temperature tuning coefficient	C _T	nm/K	0.15	0.20	0.22
current tuning coefficient	Cı	nm/mA	0.01	0.02	0.03
slow axis (FWHM)		degrees	17	20	25
fast axis (FWHM)		degrees	35	40	45
emitting area	W×H	μт х μт	3 x 1	4.5 x 1.5	5 x 2
storage temperatures	Ts	°C	- 40	+ 20	+ 80
operational temperature at case	T _c	°C	- 20	+ 25	+ 50